Pipe Hugger / LP The Original, one piece high intensity trans-inject molded, web stabilized, liquid in the bladder, pressure pulsation interceptor


Alcensed. W. Packer Since 1963

For Flow Fluctuation removal AND Pressure Pulse Interception STANDARD INVENTORY DUAL USE CONFIGURATION

Peg/--/-- SERIES


Or use the second connection to save a "T" for the system Drain, RV or PI, and specify standard low cost inventory twin connection items.

Where a "T" has already been installed Single connection options:-



PeG/FF/--Flange Faces in accordance with ANSI B16.6 # or DN--PN-- standards, also one NPTF central thread.

PeG/Plas/Plastic wetted parts. The safety of a metal enclosure stops low temp fracture, with PVC PP or Glass filled PTFE, thread & ANSI 150# or DN-PN16 flange face




Because our bladders are stabilized by WEBS (see section view right) Dampers may be installed, liquid side Up, Down, horizontal, or at any angle.

PeG/LND/-Lined with replaceable elastomer same material as bladder. Flange face is small amount of "gold" etc. Other features as above


Single connection Not recommended for :-


- a. Pulsation Interception
- b.Flushing before service
- c. Frequencies above 7 Hz.
- d.Constant Temp.
- e. Particulate service.

DN PN or ANSI Flanges extra





"Off The Shelf" Inventory Standard "DUAL USE" configuration.





For Suction systems with single head metering pumps that have vertically down check valve connections Please see this style on Drwg. PhrLpVw





L

C/C

C/C = Connection to Connection

PROCESS LIQUID
STAINLESS WETTED Pts.
CARBON St. N2 CUSHION BONNET

CUSHION PRE-FILL

When also Was 1884					
Item	Part No.	Description	Material	I.D. #	CUSTOMER:
1	SK15171	N ₂ Prefill	304ss		CUSTOMER REF.:
2	-	Body			QUANTITY:
		End Closure			W/O No.:
3	DDT				WEIGHT (EST.):
4		3 Turn Roll Ring			
5		Twin port Liquid End Plug			
6		Seal - 70° IRH, A			ISSUED BY:
7		Flat Plate Anti-Extr.			CHECKED BY:
8		Webbed Liquid Bladder			ISSUE DATE:
-		Webbed Liquid Diaddel			ISSUE DATE.
l					
I	1				

R PUSC FUSION
Guard Against Pulsation

ISO 9001 - 95-LON-AQ-458
www pulseguard.co.uk
PO Box 47 Stockport "LIDI"
SK5 7BB Ches. UK
--44(0)161-442-6222
Facsimile -443-1486

PROTECTION

CE 0040 SS0210435 www.pulseguard.com Box 506 Hampstead NC 28443-9110 USA -01-910-270-2737 Fax. -01-910-270-2740 TITLE: LOW COST PROCESS DAMPER with in place flushability to:TO PREVENT SUCTION SYSTEM LOSSES FROM ACCELERATION HEAD
& FOR PRESSURE PULSATION INTERCEPTION UP TO 1000psi / 70Br.

Typical Application: Zero pressure loss by no flow reversal makes PIPEHUGGER LP ideal for - CHEMICAL METERING SYSTEMS, MIXING SYSTEMS, PAINT & COATING DOSSING, AND LIQUID TRANSFER PUMP PACKAGES, FOR LIQUIDS THAT ARE USED IN BATCH AND CAMPAIGN PRODUCTION NEEDING CONSTANT TEMP. OR CLEANING IN PLACE BEFORE THE NEXT RUN.

FILE REF: LpPhrVw.bmp

SCALE: NTS ALL DIMENSIONS ARE IN MM EXCEPT AS STATED.

Cut Sheet/ "Drawing"/ Dimensioned View, Nbr.

Peg/TW

SHEET: 1 OF 1

REV. 0