


PART Nbr. & ID

PLAS. TYPE/Volume/Membrane -Mtl./Pressure/Connections/ Plastic Mtl.  
PiG-Plas / TW/ ---i (i=in3)/B=Gas Bag mm x Lgth -?/---p (p=psi)/to Pmp.- to Sys./ PVC or PP  
Metric - PiG-Plas / TW/---Lt =Litres/B=bag diam mm x Lgth -?/---Br=Bar)/to Pmp.- to Sys./Shell Material



**FOR THE SAME PRICE AS A SPARES KIT** Nitrogen Process Liquid Separator Membrane Plastic

we will supply and fit a spares kit and recertify your damper for you  
This way, you allow us to see as many of our products back as possible,  
and we learn the improvements that you need.


It is part of our ISO 9001 continuous improvement policy.



As a manufacturer of vessels to ASME VIII Div. 1 we believe in regular corrosion inspection and re hydro testing.

To return an item for service, first call to ask for a RGA / RMA (Return Goods/Mtl Authorization) Nbr.

Item 2, Gas Bag part numbers are the outside diameter mm at the sealing bead followed by the Over All Length  
B= Gas Bag Example: B98-300-? where?=the bag material. N=ButadieneAcryloNitrile, E=EthylenePropyleneTerPolymer  
V=FluoroCarbonElastomer, B=Butyl, H=ChloroSulphonated Polyethylene "Hypalon", S=Silicone Rubber, Nat=Natural Rub.  
To order spares : SK=Spares Kit Example SK-B98x300-E includes the gas Bag and the necessary seals also.



*Dampers that do. Flow goes through. BUT Pressure Pulsation does not.*

**PULSE GUARD** Inc. Guard against Pulsation

In USA Toll Free, 1-888-DAMPERS (326-7377)  
For the Americas --01(1)910-270-2737  
BW & Color Fax, --01(1)910-270-0320  
Color fax is 10 times faster than email attach, and there are no viruses.

